



6' Plugmold Tamper-Resistant Multioutlet System

Features & Benefits

Meets new Tamper Resistant requirements for 2008 NEC Section 406.11. Provides additional protection from burns and other injuries. Mandated for residential applications.

Available in 3' & 5' [914mm & 1.5m] lengths with 6" [305mm] receptacle spacing. Provides additional power access in smaller, more confined areas. Multiple lengths present more mounting options.

Steel or aluminum construction. Superior strength for residential applications. Providing years of protection and convenience.

Multiple finishes. Available in ivory, gray, white, black, stainless steel and anodized aluminum to accommodate a wide range of applications.

Custom options available. Custom configurations and finish options are also available. Consult the factory for more information.

This product meets the material restrictions of RoHS.

Built-in shutter system. Prevents the insertion of unwanted objects such as hairpins, keys and nails. Providing additional protection for occupants including small children.

15A Proprietary Simplex Decorator Receptacle. Functional and aesthetically pleasing, matches any décor.

Designed for surface mounting. Easier and more convenient installation. Eliminates the need to break through walls.

Multiple power feed options. Provide clean, attractive installations with concealed power sources.

cULus Listed.

Specifications

General Info

UPC Number	786776185393	Country Of Origin	United States
Product Line	Wiremold	Application Sector	Residential/Commercial
Type	Plugmold	Number of Receptacles	10

Standard

Multi-Outlet Assemblies: File E15191
Guide PVGT Meets Article 380 of NEC.

Listing Agencies / 3rd Party Agencies

cULus Listed

Yes

cULus ListingNumber

E15191

Buy American Act Compliance

NAFTA

Yes

Additional Information

RoHS Conformant

Yes

Product Environmental Profile

Yes

Technical Information

Voltage

125 V

Frequency Rating

60 Hz Hz

Enclosure Type

Steel

Environmental Conditions

Dry Interior Locations
