



Tamper-Resistant Spec Grade Receptacles, Back and Side Wire, 20A, 125V

Features & Benefits

Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects. Auto-ground clip assures positive ground.

Extra heavy-duty brass, one-piece mounting strap with integral ground. One-piece, brass, triple-wipe power contacts for lasting retention.

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body. Impact-resistant nylon face and back body.

Two drive screws anchor strap to back body and face. Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection. Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

| | | | |
|-----------------------|----------------|-------------------|----------------------------------|
| Product Line | Pass & Seymour | Color | Ivory |
| UPC Number | 785007268010 | Country Of Origin | Mexico |
| Number of Receptacles | 2 | Outlet Type | Tamper-Resistant |
| Application Sector | Commercial | Standard | UL498, CSA C22.2 No. 42, FEDSPEC |
| Type | Outlet | | |

Dimensions

| | | | |
|-------------------|----------|------------------|--------|
| Product Width US | 1.625 in | Product Depth US | 0.9 in |
| Product Height US | 2.75 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|---------------------|--------------------------|--------------------------|-----------------------|
| Dielectric Strength | Withstands 2000V minimum | Is Tamper-Resistant | Yes |
| Connection | Back and side wire | Number of Wires | 3 |
| Temperature Rating | -40° - 60° C | Amperage | 20 A |
| Number of Poles | Double Pole | Wire Size | 14 - 10 AWG |
| Indoor/Outdoor | Indoor | Environmental Conditions | Flammability: UL94 V2 |
