




Wiremold  
2400D Divided Radiused Internal Elbow Fitting  
Part No. V2417DFO



90 degree, divided internal corner elbow provides 2" (51mm) cable bend radius control for fiber optic and UTP/STP cable installations. Two couplings included.

## Features & Benefits

90 degree, divided internal corner elbow provides 2" (51mm) cable bend radius control for fiber optic and UTP/STP cable installations. Two couplings included.

## Specifications

### General Info

Product Line	Wiremold	Color	Ivory
UPC Number	786776569605	Country Of Origin	United States
Application Sector	Commercial, Residential	Standard	cULus Listed Raceway: File E4376 Guide RJBT. Fittings: File E41751 Guide RJPR. Base & Blank Cover: Meets Article 386 of NEC. Meets Section 12-600 of CEC.
Type	Raceway		

### Dimensions

Product Weight US	0.77 lb
-------------------	---------

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E41751	cULus Listed	Yes
---------------------	--------	--------------	-----

---

Additional Information

---

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

---

Technical Information

---

Voltage	600.0 V
---------	---------

---