



Pass and Seymour  
**Tamper-Resistant Isolated Ground Decorator Hospital Grade Receptacle, Back and Side Wire, 20A, 125V, Red**  
Part No. TRIG26362HGRED



Tamper-Resistant Isolated Ground DecoratorHospital Grade Duplex Receptacle, Back and Side Wire, 20amp 125volt, White.For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

### Features & Benefits

IG symbol and Isolated Ground markings for easy identification and circuit delineation.	Triple-wipe brass contacts ensure lasting, positive contact with plug blades.
High-impact resistant nylon face resists impacts and scrapes.	Corrosion-resistant plated steel strap.
Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.	Plastic barrier isolates grounding terminal from mounting strap and metal boxes.
Side and internal screw-pressure-plate back wire capability with #14 - #10 AWG copper or copper-clad, solid or stranded wire.	Auto-ground clip assures positive ground.
For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .	For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, <a href="#">click here</a> .
Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact	

### Specifications

#### General Info

Product Line	Pass & Seymour	Color	Red
Country Of Origin	Mexico	Application Sector	Commercial
Standard	cULus UL498		

#### Dimensions

Product Width US	1.187 in	Product Depth US	1.25 in
Product Height US	3.625 in		

#### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
Connection	Back and side wire	Number of Wires	3
Temperature Rating	-40° - 60° C	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Voltage	125.0 V	Environmental Conditions	Flammability: UL94 V2