



Pass and Seymour

Weather-Resistant Commercial Grade Receptacles, Gray
Part No. WR20TRGRY

Weather-Resistant Commercial Grade Receptacles, 20 amp, 125 volts, Ivory, WR20TRI



Features & Benefits

Auto-ground clip assures positive ground.

WR marking on face as required by UL Standard.

Zinc-plated steel mounting screws for greater ease of installation and removal in wet or damp locations.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Tri-drive brass terminal screws. Internal screwpressure plate back and side wire capability. Two back wire holes for more wiring flexibility.

Heavy-duty, brass strap for added strength and ground conductivity.

UV-resistant nylon face for longer life under adverse environmental conditions.

Two drive screws anchor strap to backbody and face where abrupt removal torque is strongest.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

.032 inch thick brass triple-wipe power contacts for lasting retention.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Color	Gray	UPC Number	785007243222
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Commercial	Standard	UL 498

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140596
--------------	-----	---------------------	--------

Technical Information

Number of Poles	Double Pole	Voltage	125 V
Phase	3	Wire Size	10-14Awg
Number of Wires	3		