



Wattstopper
Ultrasonic Ceiling Occupancy Sensor, 24VDC, 500 sq ft
Part No. UT-300-1



Wattstopper's UT-300 Ultrasonic Ceiling Sensors automatically turn lighting on and off based on occupancy. The sensors mount on the ceiling with a flat, unobtrusive appearance and provides 360° coverage.

Features & Benefits

Architecturally appealing low-profile appearance

Accepts low-voltage switch input for manual-on operation

Walk-through mode increases savings potential

Ultrasonic diffusers give more comprehensive coverage

Plug terminal wiring for quick and easy installation

Automatic or manual-on operation when used with a BZ-150 Power Pack

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182915149
Country Of Origin	China	Product Series	UT-300
Features	Adjustable Time Delay, Indicator Lights, Isolated Relay, Light Level Sensor, Power Pack Required, Sensitivity Adjustment	Installation Location	Ceiling
Included	Mounting Screws	Application Sector	Commercial
Standard	UL, cUL, PEP	Warranty Type	5-Year
Type	Sensor		

Dimensions

Product Width US	4.5 in	Product Weight US	0.2 lb
Product Volume US	44.4 cu in	Product Depth US	1.5 in
Product Height US	4.5 in		

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Operating Temperature Min	32 °F	Timer Type	DIP Switch
Compatibility	BZ Power Packs	Ultrasonic Frequency	40 kHz
Has Battery	No	Sensor Coverage Pattern	360 deg
Sensor Type	Occupancy	Operating Temperature Max	131 °F
Sensor Mounting Height	8-10 ft	Number of Buttons	0
Number of Rockers	0	Sensor Technology	Ultrasonic
Timer Duration	30 Seconds, 5-30 Minutes	Indicator	Ultrasonic Detection LED
Input Voltage	24 VDC/VAC	Indoor/Outdoor	Indoor
Sensor Coverage	500 sq ft	Mounting Type	4 in Octagonal J-Box, Ceiling Tile, Surface
On Function	Auto On	Current Draw	25 mA
Operating Temperature	0°-55°C, 32°-131°F	Operating Humidity	5-95% RH (Non-Condensing)
Sensing Range	24 x 24 ft	Wire Connection Type	Terminal Block
Engraving Type	Blank	Storage Temperature	23° - 176° F, -5° - 80° C