



6' Plugmold Tamper-Resistant Multioutlet System

## Features & Benefits

Meets new Tamper Resistant requirements for 2008 NEC Section 406.11. Provides additional protection from burns and other injuries. Mandated for residential applications.

Built-in shutter system. Prevents the insertion of unwanted objects such as hairpins, keys and nails. Providing additional protection for occupants including small children.

Available in 3' & 5' [914mm & 1.5m] lengths with 6" [305mm] receptacle spacing. Provides additional power access in smaller, more confined areas. Multiple lengths present more mounting options.

15A Proprietary Simplex Decorator Receptacle. Functional and aesthetically pleasing, matches any décor.

Steel or aluminum construction. Superior strength for residential applications. Providing years of protection and convenience.

Designed for surface mounting. Easier and more convenient installation. Eliminates the need to break through walls.

Multiple finishes. Available in ivory, gray, white, black, stainless steel and anodized aluminum to accommodate a wide range of applications.

Multiple power feed options. Provide clean, attractive installations with concealed power sources.

Custom options available. Custom configurations and finish options are also available. Consult the factory for more information.

cULus Listed.

This product meets the material restrictions of RoHS.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776185393
Country Of Origin	United States	Number of Receptacles	10

Application Sector	Residential/Commercial	Standard	Multi-Outlet Assemblies: File E15191 Guide PVGT Meets Article 380 of NEC.
Type	Plugmold		
Dimensions			
Product Width US	1.3 in	Product Depth US	0.75 in
Product Length US	1.3 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E15191	cULus Listed	Yes
Buy American Act Compliance			
NAFTA	Yes		
Additional Information			
RoHS Conformant	Yes	Product Environmental Profile	Yes
Technical Information			
Frequency Rating	60 Hz	Amperage	15 A
Enclosure Type	Steel	Voltage	125.0 V
Environmental Conditions	Dry Interior Locations		