adorne®
Tamper-Resistant Dual Controlled Outlet

ARCD152, ARCD202

Tamper-Resistant Dual Controlled Outlet

The adorne Dual Controlled Outlet controls both receptacles, which can be turned off for energy efficiency and cost savings. Permanent controlled receptacle marking allows for long-lasting, easy identification of controlled receptacle for end-users. NEMA-approved and compliant with 2014 NEC®, CA Title 24, and ASHRAE Energy Efficiency Standard 90.1

FEATURES & BENEFITS

adorne devices fit in all existing NEMA-approved wallboxes.

Heavy gauge steel frame is grounded via factory installed 12AWG ground lead. Device and metal wall plates are self-grounded to frame.

Device snaps into the frame and self-aligns without any screws.

STANDARD WALLBOX

FRAME

DEVICE

WALL PLATE

Wall plate snaps onto frame; no screws required.

Modular system solves device alignment problems, improving fit and finish in multi-gang installations.

Wall plate and frames available in 1-6 gang sizes.

adorne devices can be installed in any existing standard wallbox.

Backwire terminal screws are recessed into back of body.

ORDERING INFORMATION

CATALOG NUMBER	DESCRIPTION	RATING	NEMA	COMPLIANCE	COLORS	COO
ARCD152M10	15A TR Dual-Controlled Outlet	15A, 125V	5-15R		Magnesium	China
ARCD152W10	15A TR Dual-Controlled Outlet	15A, 125V	5-15R		White	China
ARCD152G10	15A TR Dual-Controlled Outlet	15A, 125V	5-15R		Graphite	China
ARCD202M10	20A TR Dual-Controlled Outlet	20A, 125V	5-20R		Magnesium	China
ARCD202W10	20A TR Dual-Controlled Outlet	20A, 125V	5-20R		White	China

VERTICAL MARKETS

- Residential
- Hospitality
- Luxury Office
- Light Commercial

COMPLEMENTARY PRODUCTS

adorne® also offers Paddle Style Dimmers and Fan Control Devices to pair with our Paddle Style Switches for an overall, aesthetically pleasing and multi-functional installation.

adorne® Wall Plates provide the perfect complement to adorne Switches, Dimmers, Outlets, and Accessories. The collection includes a variety of finishes, from metals to leather and wood, as well as plastic plates that are available in contemporary and classic colors.

Each wall plate is packaged with a metal frame to enable easy installation when paired with a device. All plates are screwless and simply snap onto the included metal frame.

All adorne wall plates are UL and ETL-approved.

2-Module
Paddle Dimmer

2-Module
Paddle Fan
Speed Control

1-Module
Paddle Switch

TECHNICAL SPECIFICATIONS

3rd Party Compliance

cULus Listed, File Number E140597, Standard UL20.



Performance

ELECTRICAL

Maximum Working Voltage	120VAC
Current Rated	15A, 20A Feed Through
Temperature Rise	30°C Maximum at full-rated current

MECHANICAL

Back Wire	With internal pressure plates, #8-32 screw
Terminal Accommodations	#14AWG-#12AWG

ENVIRONMENTAL

Flammability	UL94 V2



Materials

Face	Polycarbonate	Terminal	Brass
Back Body	Polycarbonate	Termination	Steel Plated Scews
Contacts	Silver		

Warranty

Limited Lifetime Warranty

COMPLEMENTARY DEVICES & ACCESSORIES

sofTap™
Switches & Dimmers – designed with an innovative micro-movement that turns lights on and off with just a soft "tap" of the finger.

SensaSwitch™
Switches & Dimmers – Sensor turns lights on when you enter a room and off when you leave. (Also available in Manual-ON/Auto-OFF format.)

Whisper™
Switches & Dimmers – A smart design that features elegant lines and a quiet, fluid motion.

Touch™
Switches & Dimmers – A stunning translucent face works just like an iPhone® — simply touch your finger on the circle to turn lights on and off.



Paddle™
Switches, Dimmers & Fan Speed Controls – A wide, graceful curve works with a simple up-and-down motion, allowing you to turn lights on and off with ease.



Wave™
Switches – Smart technology combined with sleek, modern design. Simply wave your hand to turn lights on and off.

Push™
Switches – A tactile, finger-sized impression lets you turn lights on and off with a simple push-button motion.



Tamper-Resistant Outlets/ Tamper-Resistant GFCI Outlets

USB Charging Outlets

Nightlight/Portable Nightlight Flashlight

PLUS: Compatible Wall Plates, Accent Lights, Locator Lights, Under-Cabinet Lighting System

NOTE: All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

NOTE: The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

Canada
905.738.9195
www.legrand.ca

FOLLOW US

©2019 Legrand All Rights Reserved SF20267R1