

**PlugTail™. The fastest, most consistent and reliable wiring devices – ever.**

PTTR5262, PTTR5362, PTTR26262, PTTR26362,  
PTTR5262SC, PTTR5362SC, PTTR26262SC, PTTR26362SC

Factory-terminated devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle. The connector simply snaps into the back of the device – no fussing with wires, stripping, or tightening screws. PlugTail devices are finger safe with no exposed terminals, so taping is not required. Now device installation is a snap!

A sturdy mechanical shutter system helps prevent children from sticking objects into the receptacle. The toughest and safest tamper-resistant receptacle available. They are offered in both duplex and Decorator style, in addition to split circuit versions.

## Features & Benefits

**Auto-ground clip** assures positive ground.


**Built-in connector** features large brass terminal blades to ensure consistent, reliable electrical connections.

**High performance copper alloy contacts** snugly terminate on device blade terminals. Audible snapping latch assures connection, allows release.

**.036 inch thick, brass, triple-wipe power contacts** for lasting retention.

**Dual mechanical shutter system** to help prevent insertion of foreign objects.

**Plated steel wrap strap design** for maximum durability and corrosion resistance.



PTTR5362I

**Ultrasonically welded polycarbonate connector housing** secures terminations and conductors in a UL Listed, finger safe housing.

**Pre-stripped connector leads** fasten to conductors, easier than standard pigtailed.



**Split circuit versions are pre-wired with one welded pre-stripped wire lead** to facilitate switched receptacle circuit applications.

**No exposed terminals** create a finger safe application before, during, and after installation.

## 3rd Party Compliance



cULus Listed, File Number E140596, Standard UL498.  
Federal Specification WC596.  
Conforms to NEMA WD-1 and WD-6.

## Technical Information

### Performance

#### Electrical


Dielectric Withstand Voltage	Withstands 2000V minimum
Maximum Working Voltage	125V
Current Interrupting	Certified for current interrupting at full-rated current (receptacle only)
Temperature Rise	Maximum 30° C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current

#### Mechanical


PlugTail Connector Identification	#12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only
Product Identification	Ratings are permanent part of the device

#### Environmental

Flammability	UL94 V2
Operating Temperature	Maximum continuous +60°C, minimum -40°C (without impact)



**Dimensions for  
15 & 20 Amp**



**Dimensions for  
15 & 20 Amp**

### PlugTail Receptacle Materials


Face	Nylon	Line Contacts	.036 688 Brass
Integral Ground System	.036 260 Brass	Auto Ground Clip	Steel
Back Body	PVC	Mounting Strap	.042 Zinc-Plated Steel
Assembly Drive Screw	Zinc-Plated Steel	Mounting Screws	Tri-Drive Steel
Tamper Shutter	Thermoplastic		

### PlugTail Connector Materials

Housing	Polycarbonate	Contacts	.030 Copper Alloy
---------	---------------	----------	-------------------

### Warranty

1 Year



**PTR66STR**

**PTR66STRBP**

**PTR66STRG**



**15 & 20 Amp Split  
Circuit Versions**

## Ordering Information

### Duplex Receptacles

Catalog Number	Ratings	Color	NEMA Config.
PTTR5262I	15A 125V	Ivory	5-15R
PTTR5262W	15A 125V	White	5-15R
PTTR5262	15A 125V	Brown	5-15R
PTTR5262BK	15A 125V	Black	5-15R
PTTR5262LA	15A 125V	Light Almond	5-15R
PTTR5362I	20A 125V	Ivory	5-20R
PTTR5362W	20A 125V	White	5-20R
PTTR5362	20A 125V	Brown	5-20R
PTTR5362BK	20A 125V	Black	5-20R
PTTR5362LA	20A 125V	Light Almond	5-20R

### Split Circuit Duplex Receptacles with 6" Lead

Catalog Number	Ratings	Color	NEMA Config.
PTTR5262SCI	15A 125V	Ivory	5-15R
PTTR5262SCW	15A 125V	White	5-15R
PTTR5262SC	15A 125V	Brown	5-15R
PTTR5262SCBK	15A 125V	Black	5-15R
PTTR5262SCLA	15A 125V	Light Almond	5-15R
PTTR5362SCI	20A 125V	Ivory	5-20R
PTTR5362SCW	20A 125V	White	5-20R
PTTR5362SC	20A 125V	Brown	5-20R
PTTR5362SCBK	20A 125V	Black	5-20R
PTTR5362SCLA	20A 125V	Light Almond	5-20R

### Decorator Receptacles

Catalog Number	Ratings	Color	NEMA Config.
PTTR26262I	15A 125V	Ivory	5-15R
PTTR26262W	15A 125V	White	5-15R
PTTR26262	15A 125V	Brown	5-15R
PTTR26262BK	15A 125V	Black	5-15R
PTTR26262LA	15A 125V	Light Almond	5-15R
PTTR26362I	20A 125V	Ivory	5-20R
PTTR26362W	20A 125V	White	5-20R
PTTR26362	20A 125V	Brown	5-20R
PTTR26362BK	20A 125V	Black	5-20R
PTTR26362LA	20A 125V	Light Almond	5-20R

### Split Circuit Decorator Receptacles with 6" Lead

Catalog Number	Ratings	Color	NEMA Config.
PTTR26262SCI	15A 125V	Ivory	5-15R
PTTR26262SCW	15A 125V	White	5-15R
PTTR26262SC	15A 125V	Brown	5-15R
PTTR26262SCBK	15A 125V	Black	5-15R
PTTR26262SCLA	15A 125V	Light Almond	5-15R
PTTR26362SCI	20A 125V	Ivory	5-20R
PTTR26362SCW	20A 125V	White	5-20R
PTTR26362SC	20A 125V	Brown	5-20R
PTTR26362SCBK	20A 125V	Black	5-20R
PTTR26362SCLA	20A 125V	Light Almond	5-20R

Catalog Number	Wire Type	Wire Length
----------------	-----------	-------------

### PlugTail Connectors - Right Angle


PTRA6SOL	Solid	6"
PTRA6STR	Stranded	6"
PTRA6SOLB25	Solid	25"
PTRA6STRB25	Stranded	25"

### PlugTail Connectors - Right Angle

PTRA6SOL	Solid	6"
PTRA6STR	Stranded	6"

### PlugTail Connectors - Right Angle

PTRA6SOLG	Solid	6"
PTRA6STRG	Stranded	6"



---


## Vertical Markets

- Office/Retail
- Institutional
- MDU
- Entertainment
- Hospitality/Lodging
- Education

---

## Also available...

- Hospital Grade Devices
- Straight Blade Plugs & Connectors
- IEC 309 Industrial Products
- TVSS & Isolated Ground Devices
- Turnlok® Locking Devices
- Flexcor® Wire Mesh Grips
- Ground Continuity Monitoring (GCM)
- Weatherproof Boxes & Covers
- Bulk Solutions

 The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



**Legrand, North America**  
60 Woodlawn Street  
West Hartford, CT 06110  
1.877.BY.LEGRAND (295.3472)  
[www.legrand.us](http://www.legrand.us)

**Canada**  
905.738.9195  
[www.legrand.ca](http://www.legrand.ca)

FOLLOW US

