




## Wiremold

Plugmold 5' Alternating USB Tamper Resistant Multioutlet System in White  
Part No. WH20GB509TRUSBA



The Wiremold 2000 Series raceway offers a selection of steel, aluminum, and nonmetallic raceways that provide a versatile solution for many applications. Plugmold sections offer single or alternating circuits, in standard or isolated ground receptacles. The ScuffCoat finish is scratch resistant and protects against nicks and chips while preventing color from fading.

### Features & Benefits

USB charging. Dual-port charging modules share 2.4 amps of charging capacity and can charge multiple phones, tablets or other mobile devices at the same time. Multiple colors and finishes. Painted finishes of black, gray, ivory, and white, as well as anodized aluminum and stainless steel versions integrate easily with any room decor. Compact design. Low-profile design installs in tight locations while offering multiple power and USB charging connections. Receptacle spacing accommodates bulky AC adapters.

Tamper-resistant receptacles. Prevents the insertion of foreign objects into receptacles reducing the risk of shocks or electrocution. Meets 2014 NEC section 406 requirements.

### Specifications

#### General Info

Color	White	UPC Number	786776184471
Country Of Origin	United States	Product Line	Wiremold
Application Sector	Residential/Commercial	Type	Plugmold
Number of Receptacles	3	Standard	cULus Listed Multioutlet Assembly: File E15191 Guide PVGT/PVGT7

#### Dimensions

Product Volume US	66.0 cu in	Product Width US	60.0 in
Product Height US	1.25 in	Product Weight US	3.12 lb
Product Depth US	0.88 in		

#### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	E15191
--------------	-----	---------------------	--------

#### Buy American Act Compliance

NAFTA	Yes		
-------	-----	--	--

#### Additional Information

RoHS Conformant	Yes	Product Environmental Profile	Yes
-----------------	-----	-------------------------------	-----

---

Technical Information

---

Voltage

125 V

Frequency Rating

60 Hz

---

Enclosure Type

Steel

Environmental Conditions

Dry interior locations.

---