



## Wiremold

Wiremold 20GB612 Plugmold Multioutlet System in White  
Part No. WH20GB612



The Wiremold 2000 Series raceway offers a selection of steel, aluminum, and nonmetallic raceways that provide a versatile solution for many applications. Plugmold sections offer single or alternating circuits, in standard or isolated ground receptacles. The ScuffCoat finish is scratch resistant and protects against nicks and chips while preventing color from fading.

### Features & Benefits

Steel Raceway. Provides superior strength for any dry location installation.

Compact, low profile appearance. Requires minimal space.

Available in Ivory ScuffCoat or gray baked enamel finish. The durable ScuffCoat provides a durable, scratch-resistant finish while the gray baked enamel compliments the décor or can be painted.

Full range of fittings. Provides a complete wiring solution.

Single-and-dual-gang boxes. Wire devices into the raceway system or protect a Plugmold® strip with a surge or GFCI device.

Factory wired Plugmold® sections available in 3', 5', and 6' lengths with 15A receptacles installed in cover. Ideal for short runs requiring additional outlets in electrically busy areas.

Single, alternating circuit, and isolated ground receptacles. Meets virtually any job requirement.

Choice of receptacle spacing. Center spacing between receptacles of 6", 9", 12", and 18".

Snapicoil harnesses of prewired receptacles in 48' and 50'. Eliminates multiple splicing, speeding up installation on long runs.

Snapicoil harnesses offer a choice of receptacle spacing. Center spacing between receptacles of 12", 18" and 30".

Customization available. All products can be modified to accommodate virtually any application.

This product meets the material restrictions of RoHS.

### Specifications

#### General Info

Color	White	UPC Number	786776074468
Country Of Origin	United States	Product Line	Wiremold
Application Sector	Residential/Commercial	Type	Plugmold
Number of Receptacles	6	Standard	cULus Listed Multioutlet Assembly: File E15191 Guide PVGT/PVGT7

#### Dimensions

Product Volume US	74.52 cu in	Product Width US	72.0 in
Product Height US	1.38 in	Product Weight US	3.31 lb
Product Depth US	0.75 in		

#### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	E15191
--------------	-----	---------------------	--------

#### Buy American Act Compliance

---

NAFTA	Yes
-------	-----

---

Additional Information

---

RoHS Conformant	Yes	Product Environmental Profile	Yes
-----------------	-----	-------------------------------	-----

---

Technical Information

---

Voltage	125 V	Frequency Rating	60 Hz
---------	-------	------------------	-------

---

Enclosure Type	Steel	Environmental Conditions	Dry interior locations
----------------	-------	--------------------------	------------------------

---