



The Q-Series Wall Mounted fiber enclosure system is designed to support standard density LAN or POL applications in building networks. The all steel chassis enables reliable protection and management of fiber optic cable patching, splicing, and connecting. The enclosure also enables distribution of backbone cabling to active equipment, switching, or cross/interconnect horizontal area. The 1 panel footprint accommodates up to 24 LC fibers, the 2 panel accommodates up to 48 LC fibers, while the 4 panel accommodates up to 96 LC fibers. Each enclosure is compatible with OFP Adapter Panels, Compact 12 Fiber Splice Trays, and LM2 Pre-terminated or M2 Splice Cassettes.

## Features & Benefits

### Standard Density

Accepts 12 or 24 fiber LM2 pre-terminated or M2 splice cassettes, FST4-F012 splice tray (WQS-02P & WQS-04P only)

### Low-Profile Design

Providing unobtrusive protection and management of all enclosed cabling infrastructure

### Cable Ingress and Egress

Four ingress or egress points with rubber grommets help to protect and route all connectivity infrastructure.

### Cable Management

Protect and safely route all sensitive fibers with the included cable management system, central strength member bracket, and bend limiters

### Low-Profile Design

Providing unobtrusive protection and management of all enclosed cabling infrastructure

### Cable Management

Protect and safely route all sensitive fibers with the included cable management system, central strength member bracket, and bend limiters

## Specifications

### General Info

Product Line	Ortronics	UPC Number	662875029182
Country Of Origin	Taiwan, Province Of China	Included	Rubber grommets, labels, cable management clips, cable cradle,
Type	Enclosure		

### Technical Information

Compatibility	OFP/M2/LM2	Frame	Steel
Mounting	Wall		