legrand®

Pass & Seymour

Isolated Ground PlugTail™ Receptacles 15 & 20A, 125V

PTIG5262, PTIG5362

PlugTail™ — The fastest, most consistent and reliable wiring devices – ever.

Factory-terminated devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle. The connector simply snaps into the back of the device — no fussing with wires, stripping, or tightening screws. PlugTail devices are finger safe with no exposed terminals, so taping is not required. Now device installation is a snap!

The toughest and safest isolated ground receptacle available.



FEATURES & BENEFITS

Auto-ground clip assures positive ground.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Large brass contacts snugly terminate on device blade terminals. Audible snapping latch assures connection, allows release.

Plastic barrier isolates grounding terminal from mounting strap and metal boxes.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Three drive screws anchor strap to back body and face.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Plated steel wrap strap design for maximum durability and corrosion resistance.

PTIG5362-LA

No exposed terminals create a finger safe application before, during, and after installation.

FIELD USES/VERTICAL MARKETS

- Industrial
- Retail
- Health Care
- Office
- Education
- Hospitality/Lodging
- Institutional

legrand®
Pass & Seymour

Isolated Ground PlugTail™ Receptacles
15 & 20A, 125V

ORDERING INFORMATION

Catalog Number	Rating A.	Rating V.	Color	NEMA Config. No.
Duplex Receptacles				
PTIG5262-I	15	125	Ivory	5-15R
PTIG5262-W	15	125	White	5-15R
PTIG5262	15	125	Orange	5-15R
PTIG5262-GRY	15	125	Gray	5-15R
PTIG5262-RED	15	125	Red	5-15R
PTIG5262-LA	15	125	Light Almond	5-15R
PT5362-I	20	125	Ivory	5-20R
PT5362-W	20	125	White	5-20R
PT5362	20	125	Orange	5-20R
PT5362-GRY	20	125	Gray	5-20R
PT5362-RED	20	125	Red	5-20R
PT5362-LA	20	125	Light Almond	5-20R

Catalog Number	Wire Type	Wire Length
PlugTail Connectors — Right Angle		
PTRA6STR	Stranded	6"
PTRA6SOL	Solid	6"



NEMA 5-15R NEMA 5-20R

For more information on these and other P&S products refer to our Catalog or visit our web site.

PlugTail™ Isolated Ground Receptacles
15 & 20A, 125V

legrand®
Pass & Seymour

TECHNICAL SPECIFICATIONS

3rd Party Compliance

cULus Listed, File Number E140596, Standard UL498.
Federal Specification WC596.

Performance

Electrical	
Dielectric Voltage	Withstands 2000V minimum
Maximum Working Voltage	125V
Current Interrupting	Certified for current interrupting at full-rate current (receptacle only)
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current
Mechanical	
PlugTail Connector Identification	#12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only
Product Identification	Ratings are a permanent part of the device
Environmental	
Flammability	UL94 V2
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact

PlugTail™ GFCI Receptacle Materials

Face	Nylon	Internal Ground System	.036 260 Brass
Body	PVC	Assembly Drive Screw	Zinc-Plated Steel
Contacts	.036 688 Brass	Aut-Ground Clip	Steel
Mounting Strap	.042" Zinc-Plated Steel	Mounting Screws	Tri-Drive Steel

Plug Tail Connector Materials

Housing	Polycarbonate	Contacts	.030 Brass

Warranty

1 Year



Dimensions for
15 & 20 Amp



PTRA6STR

COMPLEMENTARY DEVICES & ACCESSORIES



PLUGTAIL™ DEVICES

- Spec Grade
- Decorator
- Hospital Grade
- Tamper-Resistant
- Isolated Ground
- Split Circuit

STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Hard Use
- Construction Grade
- Construction Grade Leaded
- Commercial Grade

DECORATOR DEVICES

- Construction Grade Switches
- Specification Grade Combo Switches
- Construction Grade Receptacles
- Commercial Grade Receptacles
- Specification Grade Hallway Lights



SWITCHES

- Heavy-Duty Toggle
- Heavy-Duty Lighted Toggle
- Heavy-Duty Security
- Heavy-Duty Locking
- Construction Grade Toggle
- Commercial Grade Toggle



GFCIs

- Specification Grade
- Hospital Grade

WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Screwless Polycarbonate
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers

ALSO AVAILABLE...

- Hospital Grade Devices
- TVSS & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Bulk Solutions

Legrand/Pass & Seymour
P.O. Box 4822
Syracuse, NY 13221-4822
800-223-4185

North America Headquarters
60 Woodlawn Street
West Hartford, CT 06110
Phone: 1.877.BY.LEGRAND (295.3472)
Fax: 1.860.232.2062
www.legrand.us

Legrand Canada
570 Applewood Crescent
Vaughan, ON, L4K 4B4
Phone: 905.738.9195
Fax: 905.738.9721
www.legrand.ca

SF1506R2 – Updated May 2010 – For latest specs visit www.legrand.us/passandseymour

© 2011, Legrand/Pass & Seymour EWS/GGXTP