



Tamper-Resistant, Weather-Resistant Commercial Grade Receptacles, 20A, 125V



Features & Benefits

Auto-ground clip assures positive ground.

Zinc-plated steel mounting screws for greater ease of installation and removal in wet or damp locations.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Tri-drive brass terminal screws. Internal screw pressure plate back and side wire capability. Two back wire holes for more wiring flexibility.

Heavy-duty, brass strap for added strength and ground conductivity.

Two drive screws anchor strap to backbody and face where abrupt removal torque is strongest.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

.032 inch thick brass triple-wipe power contacts for lasting retention.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
Operating Temperature: Maximum continuous +50°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
UPC Number	785007242553	Country Of Origin	Mexico
Number of Receptacles	2	Features	Brass Mounting Strap, Weatherproof

Outlet Type	Tamper-Resistant, Weather-Resistant	Application Sector	Commercial
Wall Plate Included	No	Standard	UL498, CSA C22.2 No. 42
Warranty Type	1-Year Limited Warranty		
Dimensions			
Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140596	cULus Listed	Yes
Technical Information			
Operating Temperature Min	-40 °C	Dielectric Strength	Withstands 1500V minimum
Is Tamper-Resistant	Yes	Connection Location	Side Only
Number of Wires	3	Operating Temperature Max	60 °C
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Outdoor
NEMA Configuration Code	5-20R	Operating Temperature	-40°-60°C
Wire Connection Type	Internal Pressure Plates, Screw Terminals	Voltage	125.0 V
Environmental Conditions	Flammability: UL94 V2		