NV-T2FAM Tuner.

Specifications

Power Requirements	
AC Power Input	90-264 VAC 50/60Hz
Power Consumption, operating	3 W max.
Power Consumption, standby	1 W max.
Memory Backup	Indefinite
FM	
Tuning Range	87.5 to 108.0 MHz
Total Harmonic Distortion (1kHz)	
Mono	0.3%
Stereo	0.5%
Signal to Noise Ratio	
Mono	80dB
Stereo	75dB
Usable Sensitivity	1.0 µV
Selectivity (400 kHz)	50dB
Frequency Response (20 Hz to 15 kHz)	-3dB
Stereo Separation (1 kHz)	43dB
Antenna Input	75Ω (unbalanced)
Usable Sensitivity, 30dB S/N	14dBV
Auto Scan Sensitivity	Adjustable
Image Rejection	50dB min.
Limiting Sensitivity	10dBV
Intermediate Frequency	10.7 MHz
AM	
Tuning Range	522 to 1720 kHz
Signal to Noise Ratio	50dB
Usable Sensitivity	18 µV
Intermediate Frequency	450 kHz
Usable Sensitivity, 25dB S/N	14dBV
Auto Scan Sensitivity	Adjustable
Image Rejection	50dB min.
Audio Output	Two Stereo Outputs
Level	Adjustable
Impedance	560 ohm
Infrared Input	
Input Voltage	3-15 V
Input Carrier Frequency	38 kHz nominal
Polarity	Active High
Regulartory Approvals	
USA Safety Listing (UL 6500)	
FCC	
Canada Safety Listing (CAN/CSA E60065.00)	
Physical Specifications	
Unit Size (mm)	44 H x 430 W x 250 D
Unit Size (inch)	1.75 H x 17 W x 9.875 D
Shipping Size (mm)	205 H x 515 W x 343 D
Shipping Size (inch)	8 H x 20 1/4 W x 13 1/2 D
Unit Weight (kg)	2.36
Unit Weight (lbs)	5.20
Shipping Weight (kg)	6.5
Shipping Weight (lbs)	14.3

NuVo reserves the right to change specifications without notice.

Office Toll Free: 866.796.4904
Office Direct: 859.817.7200
Email: sales@nuvotechnologies.com
Web: www.nuvotechnologies.com