





CAUTION: TERMINATE JACKS PER SPECIFIED WIRING SYSTEM 'T568A' or 'T568B'.




NOTE: When terminating cables to jacks, lace wires from the center to the outside of the module. Install stuffer caps after terminating the cable.


THIS DEVICE IS INTENDED FOR INDOOR USE ON COMMUNICATION LOOP CIRCUIT WHICH HAVE BEEN ISOLATED FROM THE PUBLIC SWITCHED TELEPHONE NETWORK.

WIRING CHART

COLOR CODE LABEL	RJ25 6P6C USOC WIRING	RJ45 8P8C T568A WIRING	RJ45 8P8C T568B WIRING
WHITE/BLUE	4	5	5
BLUE	3	4	4
WHITE/ORANGE	2	3	1
ORANGE	5	6	2
WHITE/GREEN	1	1	3
GREEN	6	2	6
WHITE/BROWN		7	7
BROWN		8	8



REQUIRED TERMINATION TOOL
60300005 (TOOL & BLADE)
60300006 (BLADE ONLY)



RECOMMENDED STRIPPING TOOL
60300032 (TOOL)

Jack Module Termination:

STEP 1: Strip 2" of cable jacket off station cables.



STEP 2: Lace color coded wire pairs into 110 termination, as indicated by wiring label.

Note: Maintain cable pair twists within 1/2" (13mm) from the point of termination.

STEP 3: Place Jack on solid flat surface to terminate. Using a single wire 110 blade tool, terminate all 4 pairs. (See diagram Side 1)

STEP 4: Repeat steps 1 thru 3 until all Jack Modules are terminated. Install all supplied stuffer caps over terminated wires.

STEP 5: Snap Jack module into faceplate or set Jack module into base of surface mount box (not shown).



Note: Install lower Jacks first.



INSTRUCTION SHEET #	REV.	ECN #	ECN DATE	SHEET	DWN. BY:	DATE	CHK. BY:	DATE	APP. BY:	DATE
71601440	02	05486	11/3/2023	1 OF 1	LI WEI JUN	9/9/2019	DP	7/21/2023	FR	7/21/2023