



Wiremold
Charging Station, 2-Gang, (2) Duplex GFCI - Silver
Part No. XCSPP2GRR-SV



The Power Pedestal is ideal for areas that are already illuminated, such as outdoor dining areas. Shorter height enables use besides tables or as a lower-profile solution in landscaping. Station includes two duplex GFCI receptacles.

Features & Benefits

Combine power with area lighting in one pedestal to maximize functionality of outdoor spaces.

Durable, Premium Finishes – Available in three outdoor-rated finishes to complement your space design. Choose from black, bronze or silver.

Add up to two pairs of shelves to hold mobile devices while charging

Enables pedestal to support outdoor presentation areas and classrooms, eliminating the need to bring cables from inside a building.

Outdoor-Rated Construction – Rugged aluminum form designed for durability in all weather conditions. UL listed to NEMA 3R requirements to ensure optimal performance.

Add an A/V-Communication Kit to 3-gang versions to accommodate Wiremold AVIP plates as well as decorator A/V or communication devices.

Interior illuminates when door is open. Replace standard color-matched door with a transparent version to make devices inside more visible. Or, select a lockable door for added security or to ensure use is limited to facility personnel.

Specifications

General Info

| | | | |
|-----------------------|--------------|-------------------|-------------------|
| Product Line | Wiremold | Color | Silver |
| UPC Number | 786776186314 | Country Of Origin | Mexico |
| Number of Receptacles | 2 | Outlet Type | Weather-Resistant |

| | | | |
|---------------------------------------|---|-------------------------------|---|
| Application Sector | Commercial, Education, Entertainment, Healthcare, Hospitality, Parks, Retail, Transit | Standard | cULus Listed, File Number E479489, Guide PUPR |
| Warranty Type | 1-Year from Installation or 2-Years from Day of Sale | Type | Charging Stations |
| Installed Devices | GFCI | | |
| Dimensions | | | |
| Product Width US | 6.0 in | Product Weight US | 35.0 lb |
| Product Height US | 34.0 in | Product Length US | 8.0 in |
| Listing Agencies / 3rd Party Agencies | | | |
| cULus ListingNumber | E479489 | cULus Listed | Yes |
| Trade Programs | | | |
| USMCA | Yes | | |
| Additional Information | | | |
| RoHS Compliant | Yes | Product Environmental Profile | Yes |
| Technical Information | | | |
| Operating Temperature Min | -31 °F | Is Pre-Wired | Yes |
| Service Capacity | Single | Operating Temperature Max | 140 °F |
| Number of Gangs | 2 | Amperage | 20 A |
| Enclosure Type | NEMA 3R | NEMA Configuration Code | 5-20R |
| Number of Channels | 1 | Lighting Types | No Light |
| Operating Temperature | -31°F-140°F | | |