



PASS & SEYMOUR®

Specification Grade Weather-Resistant USB Charging Receptacles 15 & 20A, Tamper-Resistant



Spec and install the toughest outdoor USB charging receptacle in the industry

WRTR15USBAC6, WRTR20USBAC6


Install the fastest Weather-Resistant USB charging receptacle on the market. Industry-leading charging capacity of 6.0A, shared between both ports. Charge your smartphones, tablets, and laptops up to 40% faster than 3-5A USB chargers, while enjoying the added safety of tamper-resistant receptacles that meet NEC® requirements for outdoor use. These USB receptacles are UL listed to UL498 for weather resistance and comply with section 406.9 of the National Electrical Code. Protects children: patented shutter system helps prevent improper insertion of foreign objects – now with black "invisi-shutters" for an invisible effect. The external brass back wire pressure-plate and posted side-wire terminal screws make installation fast and easy. RoHS compliant.

Features & Benefits

Posted terminal screws and external back-wire pressure plates for more productive and reliable terminations.

AC USB receptacles available in 15 and 20A, 125V Specification Grade and Hospital Grade.

- Complies with Section 406.9 of the National Electrical Code for weather resistance. Multiple color options available.*
- Efficient power supply meets the Department of Energy (DoE) Level VI no-load power requirement of 100mW max for external power supplies.



WRTR20USBAC6LA

Available with (1) USB Type-A & (1) USB Type-C port or (2) USB Type-C ports to charge the latest mobile devices.

Reinforced nylon USB Type-A ports to withstand abuse over the life of the product.

Type-A and Type-C ports carry a minimum rating of 10,000 insertions.

AC USB receptacles are tamper-resistant to meet NEC. Patented shutter system – now with black "invisi-shutters" for an invisible effect preferred by end-users – helps prevent improper insertion of foreign objects.

Stainless steel auto-ground clips assure positive ground.

*Must be installed with a weatherproof cover. It is recommended that these devices are installed in a wall box measuring at least 3" x 2" x 2-1/2" to ensure proper NEC Article 314 box fill requirements. For retrofit applications a Weatherproof extension ring may be required on boxes with less depth than 2-1/2".



3rd Party Compliance



cULus Listed, UL Listed
Complies with test requirements UL 498, UL 1310, Federal Specification WC-596, CSA C22.2 No. 42, CSA C22.2 No. 223

Ordering Information

Performance

Electrical

Dielectric Withstand Voltage	Withstands 1500V minimum
Maximum Working Voltage	125V
Current Interrupting	Certified for current interrupting at full-rated current (receptacle only)
Maximum Temperature Rise	30°C after 50 cycles at full-rated current after 50 cycles of overload are 150% of rated current with direct current
No-load power draw	10.7 mW meets Department of Energy (DoE) Level VI requirement
FCC Part 15	Class B

Mechanical

Terminal Identification	Terminal Identification in accordance with UL498 (Brass, White, Green)
Terminal Accommodation	Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire
Product Identification	Ratings are a permanent part of device

Environmental


Flammability	UL94 V2 (for device cover) 5V (for device body and frame)
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact
RoHS	Compliant

Materials

Face	Polycarbonate
Body	Nylon
Contacts	CDA 260 Brass
Mounting Strap	.049" Zinc-Plated Steel
Terminal Screws	Tri-Drive Zinc-Plated Steel with Either Clear or Black Chromate For Color Identification
Ground Screw	Tri-Drive Steel with Green Chromate
Mounting Screws	Tri-Drive Steel
Auto-Ground Clip	Stainless Steel

Warranty



1 Year



Dimensional information is the same for all models.

Ordering Information
**Specification Grade Ultra-Fast Weather-Resistant USB Type A/Type C
 Chargers with Duplex Tamper-Resistant Receptacles**

Catalog Number	Description	Rating		Color	NEMA Config. No.
		A	V		
WRTR15USBAC6	Spec Grd - A/C	15	125	Brown	5-15R
WRTR15USBAC6BK	Spec Grd - A/C	15	125	Black	5-15R
WRTR15USBAC6GRY	Spec Grd - A/C	15	125	Gray	5-15R
WRTR15USBAC6I	Spec Grd - A/C	15	125	Ivory	5-15R
WRTR15USBAC6LA	Spec Grd - A/C	15	125	Light Almond	5-15R
WRTR15USBAC6W	Spec Grd - A/C	15	125	White	5-15R
WRTR20USBAC6	Spec Grd - A/C	20	125	Brown	5-20R
WRTR20USBAC6BK	Spec Grd - A/C	20	125	Black	5-20R
WRTR20USBAC6GRY	Spec Grd - A/C	20	125	Gray	5-20R
WRTR20USBAC6I	Spec Grd - A/C	20	125	Ivory	5-20R
WRTR20USBAC6LA	Spec Grd - A/C	20	125	Light Almond	5-20R
WRTR20USBAC6W	Spec Grd - A/C	20	125	White	5-20R



WRTR15USBAC6W

**NEMA
5-15R**

**NEMA
5-20R**

Vertical Markets

- Healthcare
- Hospitality/Lodging
- Education
- Office
- Airports
- Institutional
- Retail
- Multiple Dwelling

Also available

- SPD & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Plug Load Control Solutions

 The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us
905.738.9195
www.legrand.ca

