



Conveniently power mobile devices quickly and reliably outdoors without the need for bulky AC adapters.

WRR26USBAC6


**radiant®** Weather-Resistant Duplex Receptacles with USB charging capabilities are UL listed to UL498 for weather resistance and comply with section 406.9 of the National Electrical Code. Charge your smart-phones, tablets, and laptops up to 40% faster than 3-5A USB chargers with an Industry-leading charging capacity of 6.0A, shared between both ports. Enjoy the added safety of tamper-resistant receptacles that meet NEC® requirements for tamper-resistance. Protects children: patented shutter system helps prevent improper insertion of foreign objects – now with black “invisi-shutters” for an invisible effect. The external brass back-wire pressure-plate and posted side-wire terminal screws make installation fast and easy.

## Features & Benefits

**Combination AC USB receptacles** include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.

**Posted side-wire terminal screws and external back-wire pressure plates** for faster termination.

**Available with (1) USB Type-A & (1) USB Type-C port or (2) USB Type-C ports** to charge the latest mobile devices.



**Type-A and Type-C ports carry minimum rating of 10,000 insertions.**

**AC USB receptacles are tamper-resistant** to meet NEC. Patented shutter system — now with black “invisi-shutters” for an invisible effect preferred by end users — helps prevent improper insertion of foreign objects.

**Complies with Section 406.9 of the National Electrical Code for weather resistance.\***

WRR26USBACLA



- **AC USB receptacles available in 15A, 125V.**
- **Back and side wire termination options** accommodate #14 AWG – #10 AWG stranded and solid copper wire.
- **Multiple color options available.**

\*Must be installed with a weatherproof cover. It is recommended that these devices are installed in a wall box measuring at least 3" x 2" x 2-1/2" to ensure proper NEC Article 314 box fill requirements. For retrofit applications a Weatherproof extension ring may be required on boxes with less depth than 2-1/2".

## 3rd Party Compliance



cULus listed, UL listed. Complies with test requirements UL 498, UL 1310  
CSA C22.2 No. 42, CSA c22.2 No. 223

## Technical Information

### Performance

#### Electrical

Dielectric Withstand Voltage	Withstands 1500V minimum
Maximum Working Voltage	125V
Current Interrupting	Certified for current interrupting at full-rated current (receptacle only)
Maximum Temperature Rise	30°C after 50 cycles at full-rated current after 50 cycles of overload are 150% of rated current with direct current
No-Load Power Draw	10.7 mW Meets Department of Energy (DoE) Level VI requirement
FCC Part 15	Class B

#### Mechanical


Terminal Accommodation	Back and side wire termination options accommodate #14 AWG - #10 AWG stranded and solid copper wire.
Product Identification	Ratings are a permanent part of the device

#### Environmental

Flammability	UL94 V2 (for device cover) 5V (for device body and frame)
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact
RoHS	Compliant

#### Materials

Face	UV protected Polycarbonate
Back Body	Nylon
Line Contacts	CDA 260 Brass
Mounting Strap	G90 Galvanized plated steel
Terminal Screws	Tri-Drive Zinc-Plated Steel with Either Clear or Black Chromate for Color Identification
Ground Screw	Tri-Drive Steel with Green Chromate
Mounting Screws	Tri-Drive Steel



**WRR26USBACLA**

### Warranty

1 Year

## Ordering Information

### Ultra-Fast Weather-Resistant USB Type AC Chargers with Duplex Tamper-Resistant Receptacles

Catalog Number	Rating		Color	Total Charging Capacity	3rd Party Compliance		
	A	V			UL <sup>®</sup> UL498 UL1310	cUL <sup>®</sup> US	CS <sup>®</sup> C22.2 No. 42 C22.2 No. 223
WRR26USBAC6BK	15	125	Black	6 Amp	•	•	•
WRR26USBAC6I	15	125	Ivory	6 Amp	•	•	•
WRR26USBAC6LA	15	125	Light Almond	6 Amp	•	•	•
WRR26USBAC6W	15	125	White	6 Amp	•	•	•



NEMA  
5-15R

---

## Vertical Markets

- Residential
- Multiple Dwelling
- Hospitality/Lodging

---

## Also available in the radiant® collection...

- GFCI Receptacles
- Standard & Tamper-Resistant Receptacles
- Paddle Switches
- Lighting & Fan Controls
- Timers
- Combination Devices
- Adjustable Night Lights
- Screwless Wall Plates
- Sensors
- Home Automation Controls
- Wireless Qi & USB charging receptacles



The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



**Legrand, North America**  
60 Woodlawn Street  
West Hartford, CT 06110  
1.877.BY.LEGRAND (295.3472)  
[www.legrand.us](http://www.legrand.us)  
905.738.9195  
[www.legrand.ca](http://www.legrand.ca)

