

# PASS & SEYMOUR® Specification Grade Receptacles Decorator 15 & 20A, 125V

26242, 26342

## The standard for commercial Decorator receptacles.

Plated, corrosion-resistant straps, rugged nylon faces, and triple-wipe power contacts mean these receptacles will ensure consistent performance. Tri-drive, backed-out terminal screws save installation time.



### FEATURES & BENEFITS

**.032 inch thick, brass, triple-wipe power contacts** for lasting retention.

**Easily accessed break-off, line-contact connecting tab** for fast, easy split-circuit wiring.

**Tri-drive steel terminal screws.**

**Auto-ground** eliminates the necessity to terminate grounding conductor to device.

**Two drive screws anchor strap** to back body and face where abrupt removal torque is strongest.

**Corrosion-resistant, plated steel strap** locked in to face and back body to resist pulling away from face/body assembly.



### FIELD USES/VERTICAL MARKETS

- Retail
- Hospitality/Lodging
- Multiple Dwelling
- Office



# PASS & SEYMOUR®

## Specification Grade Receptacles Decorator 15 & 20A, 125V

### ORDERING INFORMATION

Catalog Number	Rating		Color	NEMA Config. No.
	A.	V.		
<b>Duplex Receptacles Back &amp; Side Wire</b>				
<b>26242I</b>	15	125	Ivory	5-15R
<b>26242W</b>	15	125	White	5-15R
<b>26242</b>	15	125	Brown	5-15R
<b>26242GRY</b>	15	125	Gray	5-15R
<b>26242BK</b>	15	125	Black	5-15R
<b>26242RED</b>	15	125	Red	5-15R
<b>26242LA</b>	15	125	Light Almond	5-15R
<b>26342I</b>	20	125	Ivory	5-20R
<b>26342W</b>	20	125	White	5-20R
<b>26342</b>	20	125	Brown	5-20R
<b>26342GRY</b>	20	125	Gray	5-20R
<b>26342BK</b>	20	125	Black	5-20R
<b>26342RED</b>	20	125	Red	5-20R
<b>26342LA</b>	20	125	Light Almond	5-20R



NEMA  
5-15R



NEMA  
5-20R

For more information on these and other P&S products refer to our Catalog or visit our web site.

# PASS & SEYMOUR®

## Specification Grade Receptacles

### Decorator 15 & 20A, 125V



#### TECHNICAL SPECIFICATIONS

#### 3rd Party Compliance

UL Listed, File Number E140596, Standard UL498.  
 Federal Specification WC596.  
 CSA/CUL approved, File Number LR16063, Standard CSA-C22.2 No. 42.

#### Performance

##### Electrical


Dielectric Voltage	Withstands 2000V minimum
Maximum Working Voltage	250V
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current

##### Mechanical

Terminal Identification	Terminal Identification in accordance with UL498 (Brass, White, Green)
Terminal Accommodation	#14 AWG – #10 AWG copper conductor only
Product Identification	Ratings are a permanent part of the device

##### Environmental

Flammability	UL94 V2
Operating Temperature	Maximum continuous +60°C, minimum -40°C (without impact)



Dimensions for  
15 & 20 Amp

#### Materials

Face	Nylon	Terminal Screws	#8 Tri-Drive Steel
Back Body	PVC		(Neutral = Nickel-Plated Steel)
Line Contacts	.032 688 Brass		
Mounting Strap	.042 Zinc-Plated Steel	Ground Screw	#8 Hex Tri-Drive Steel
Ground Contacts	.040 260 Brass	Assembly Drive Screw	Zinc-Plated Steel
		Auto-Ground Clip	Stainless Steel
		Mounting Screws	Tri-Drive Steel

#### Warranty

1 Year

For more information on these and other P&S products refer to our Catalog or visit our web site.

#### ALSO AVAILABLE...

- Hospital Grade Devices
- SPD & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips



#### Electrical Wiring Systems

P.O. Box 4822  
Syracuse, NY 13221-4822  
Phone: 1.800.776.4035  
[www.legrand.us/passandseymour](http://www.legrand.us/passandseymour)

570 Applewood Crescent  
Vaughan, Ontario L4K 4B4  
Phone: 905.738.9195  
[www.legrand.ca](http://www.legrand.ca)