



Pass & Seymour

# USB Receptacles Fed Spec Grade 15A & 20A, 125V

TR5261USB, TR5361USB

## Charge ahead with the Fed Spec grade USB receptacle.

Pass & Seymour® Fed Spec Tamper-Resistant Single Receptacles with USB Charging capabilities are designed with strength and durability in mind. They were designed for the commercial market and are capable of withstanding heavy use due to their Federal Specification certification. This product features an overall 2.1A USB charging capability, auto-ground clip, zinc-plated ground terminal screw, as well as triple-wipe brass contacts for lasting retention. The screw-pressure-plate back wiring makes installation fast and easy.



### FEATURES & BENEFITS

**Compact Design** Tamper-Resistant receptacle and two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.

**2.1A USB type A receptacle charges faster than other USB receptacles** Eliminates the need for bulky AC adapters.

**Tamper-Resistant, patented shutter system** prevents improper insertion of foreign objects. Meets 2011 National Electrical Code® Tamper-Resistant requirements.



**Stainless steel auto-ground clip** assures positive ground.

**Back and side wire terminals** accommodates #14 AWG - #10 AWG stranded and solid wire.

**Zinc-plated ground terminal screw.**

TR5261USB, TR5361USB

### FIELD USES/VERTICAL MARKETS

- Education
- Retail
- Hospitality/Lodging
- Office
- Health Care
- Institutional
- Multiple Dwelling


# USB Receptacles Fed Spec Grade 15A & 20A, 125V

## ORDERING INFORMATION

Catalog Number	Rating A.    V.	Color	NEMA Config. No.
<b>Single Receptacle with USB Charger</b>			
TR5261USBW	15    125	White	5-15R
TR5261USBLA	15    125	Light Almond	5-15R
TR5261USBI	15    125	Ivory	5-15R
TR5261USBBK	15    125	Black	5-15R
TR5261USB	15    125	Brown	5-15R
TR5261USBGRY	15    125	Gray	5-15R
TR5261USBRED	15    125	Red	5-15R
TR5261USBGN	15    125	Green	5-15R
TR5261USBGN	15    125	Green	5-15R
TR5261USBNI	15    125	Nickel	5-15R
<b>Single Receptacle</b>			
TR5361USBW	20    125	White	5-20R
TR5361USBLA	20    125	Light Almond	5-20R
TR5361USBI	20    125	Ivory	5-20R
TR5361USBBK	20    125	Black	5-20R
TR5361USB	20    125	Brown	5-20R
TR5361USBGRY	20    125	Gray	5-20R
TR5361USBRED	20    125	Red	5-20R
TR5361USBGN	20    125	Green	5-20R
TR5361USBNI	20    125	Nickel	5-20R



NEMA  
5-15R



NEMA  
5-20R

For more information on these and other P&S products refer to our Catalog or visit our web site.

# USB Receptacles Fed Spec Grade 15A & 20A, 125V



## TECHNICAL SPECIFICATIONS

### 3rd Party Compliance

ETL Tested US and Canada.  
Complies with test requirements UL 498, UL 1310.  
Fed Spec WC596, CSA C22.2 No. 42, CSA C22.2 No. 223.

### Performance

#### Electrical


Dielectric Withstand Voltage	Withstands 1500V minimum
Maximum Working Voltage	125V
Current Interrupting	Certified for current interrupting at full-rated current (receptacle only)
Temperature Rise	Maximum 30°C after 50 cycles at full-rated current after 50 cycles of overload are 150% of rated current with direct current

#### Mechanical

Terminal Identification	Terminal Identification in accordance with UL498 (Brass, White, Green)
Terminal Accommodation	#14 AWG – #10 AWG copper conductor only
Product Identification	Ratings are permanent part of the device

#### Environmental

Flammability	UL94 V2
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact



### Materials

Face	Polycarbonate
Body	Nylon
Contacts	CDA 260 Brass
Mounting Strap	.049" Zinc-Plated Steel
Terminal Screws	Tri-Drive Zinc Plated Steel with Either Clear or Black Chromate for color identification
Ground Screw	Tri-Drive Green with Green Chromate
Auto-Ground Clip	Stainless Steel
Mounting Screws	Tri-Drive Steel

### Warranty

1 Year

For more information on these and other P&S products refer to our Catalog or visit our web site.

SF20132 — Updated December 2012 — For latest specs visit [www.legrand.us/passandseymour](http://www.legrand.us/passandseymour)

## COMPLEMENTARY DEVICES & ACCESSORIES



### TURNLOK® LOCKING DEVICES

- Heavy-Duty Receptacles
- Heavy-Duty Flanged Inlets & Outlets




### GROUND CONTINUITY MONITORING (GCM)

- Extra-Hard Use Straight Blade
- Heavy-Duty Turnlok®



### STRAIGHT BLADE PLUGS & CONNECTORS

- Extra-Hard Use
- Heavy-Duty MaxGrip® M<sup>3</sup>



### SPD & ISOLATED GROUND DEVICES

- Construction Grade Isolated Ground
- Heavy-Duty Turnlok® Isolated Ground
- Heavy-Duty Isolated Ground SPD
- Heavy-Duty SPD
- Construction Grade SPD



### IEC 309 INDUSTRIAL PRODUCTS

- Fusible & Non-Fusible Mechanical Interlocks
- Fusible & Non-Fusible Safety Switches
- Pin & Sleeve Devices

## ALSO AVAILABLE...

- |                                      |                                     |                               |                            |
|--------------------------------------|-------------------------------------|-------------------------------|----------------------------|
| ■ Hospital Grade Devices             | ■ Straight Blade Plugs & Connectors | ■ Weatherproof Boxes & Covers | ■ Flexcor® Wire Mesh Grips |
| ■ SPD & Isolated Ground Devices      | ■ Turnlok® Locking Devices          | ■ IEC 309 Industrial Products | ■ Bulk Solutions           |
| ■ Ground Continuity Monitoring (GCM) |                                     |                               |                            |

**legrand®** | Pass & Seymour

P.O. Box 4822  
 Syracuse, NY 13221-4822  
 Phone: 1.800.776.4035  
[www.legrand.us/passandseymour](http://www.legrand.us/passandseymour)  
 570 Applewood Crescent  
 Vaughan, Ontario L4K 4B4  
 Phone: 905.738.9195  
[www.legrand.ca](http://www.legrand.ca)

