



Pass & Seymour


# Extra Heavy-Duty Receptacles PlugTail™ Devices Tamper-Resistant HG 15 & 20A, 125V

PTTR62H, PTTR63H

## PlugTail™. The fastest, most consistent and reliable wiring devices – ever.

Factory-terminated devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each extra heavy-duty receptacle. The connector simply snaps into the back of the device — no fussing with wires, stripping, or tightening screws. PlugTail devices are finger safe with no exposed terminals, so taping is not required. Now device installation is a snap!

A sturdy mechanical shutter system helps prevent children from sticking objects into the receptacle. The toughest and safest tamper-resistant hospital grade receptacle available.



### FEATURES & BENEFITS

**Auto-ground clip** assures positive ground.


**Built-in connector** features large brass terminal blades to ensure consistent, reliable electrical connections.

**Exclusive patented feature, circuit label on face** allows permanent circuit identification.

**.036 inch thick, brass, triple-wipe power contacts** for lasting retention.

**Dual mechanical shutter system** to help prevent insertion of foreign objects.

**Strap tabs wrap around and lock down on face** to prevent strap from separating from face and back body.



PTTR63H-W

**Large brass contacts** snugly terminate on device blade terminals. Audible snapping latch assures connection, allows release.

**Ultrasonically welded polycarbonate connector housing** secures terminations and conductors in a UL Listed, finger safe housing.

**Pre-stripped connector leads** fasten to conductors, easier than standard pigtails.

**No exposed terminals** before, during, or after installation increases safety at all phases of product life.

### FIELD USES/VERTICAL MARKETS

■ Industrial

■ Health Care

■ Education

■ Institutional

# Extra Heavy-Duty Receptacles PlugTail™ Devices Tamper-Resistant HG 15 & 20A, 125V

## ORDERING INFORMATION

Catalog Number	Rating A. V.	Color	NEMA Config. No.
<b>Duplex Receptacles</b>			
PTTR62H-I	15 125	Ivory	5-15R
PTTR62H-W	15 125	White	5-15R
PTTR62H	15 125	Brown	5-15R
PTTR62H-GRY	15 125	Gray	5-15R
PTTR62H-BK	15 125	Black	5-15R
PTTR62H-BL	15 125	Blue	5-15R
PTTR62H-RED	15 125	Red	5-15R
PTTR62H-LA	15 125	Light Almond	5-15R
PTTR63H-I	20 125	Ivory	5-20R
PTTR63H-W	20 125	White	5-20R
PTTR63H	20 125	Brown	5-20R
PTTR63H-GRY	20 125	Gray	5-20R
PTTR63H-BK	20 125	Black	5-20R
PTTR63H-BL	20 125	Blue	5-20R
PTTR63H-RED	20 125	Red	5-20R
PTTR63H-LA	20 125	Light Almond	5-20R

Catalog Number	Wire Type	Wire Length
<b>PlugTail Connectors — Right Angle</b>		
PTRA6STR	Stranded	6"
PTRA6SOL	Solid	6"



NEMA  
5-15R



NEMA  
5-20R

For more information on these and other P&S products refer to our Product Guide or visit our web site.

# Extra Heavy-Duty Receptacles PlugTail™ Devices Tamper-Resistant HG 15 & 20A, 125V



Pass & Seymour

## TECHNICAL SPECIFICATIONS

### 3rd Party Compliance

cULus Listed, File Number E140596, Standard UL498.  
Federal Specification WC596, Hospital Grade.

### Performance

#### Electrical


Dielectric Voltage	Withstands 2000V minimum
Maximum Working Voltage	125V
Current Interrupting	Certified for current interrupting at full-rated current (receptacle only)
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current

#### Mechanical

PlugTail Connector Identification	#12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only.
Product Identification	Ratings are a permanent part of the device

#### Environmental

Flammability	UL94 V2
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact



Dimensions for  
15 & 20 Amp



### PlugTail Receptacle Materials


Face	Nylon	Integral Ground System	.036 260 Brass
Back Body	Nylon	Assembly Drive Screw	Zinc-Plated Steel
Line Contacts	.036 688 Brass	Auto-Ground Clip	Brass
Mounting Strap	.050 260 Brass	Mounting Screws	Tri-Drive Steel
Tamper Shutter	Thermoplastic		

### PlugTail Connector Materials

Housing	Polycarbonate	Contacts	.036 688 Brass
---------	---------------	----------	----------------


### Warranty

1 Year




PTR6STR

## COMPLEMENTARY DEVICES & ACCESSORIES




### PLUGTAIL™ DEVICES

- Extra Heavy-Duty Spec Grade
- Extra Heavy-Duty Hospital Grade
- Extra Heavy-Duty Tamper-Resistant




### STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Hard Use
- Construction Grade
- Construction Grade Leaded
- Commercial Grade




### DECORATOR DEVICES

- Construction Grade Switches
- Specification Grade Combo Switches
- Construction Grade Receptacles
- Commercial Grade Receptacles
- Specification Grade Hallway Lights



### SWITCHES

- Heavy-Duty Toggle
- Heavy-Duty Lighted Toggle
- Heavy-Duty Security
- Heavy-Duty Locking
- Construction Grade Toggle
- Commercial Grade Toggle



### GFCIs

- Specification Grade



### WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Screwless Polycarbonate
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers

## ALSO AVAILABLE...

- |                                      |                                     |                               |                            |
|--------------------------------------|-------------------------------------|-------------------------------|----------------------------|
| ■ Hospital Grade Devices             | ■ Straight Blade Plugs & Connectors | ■ Weatherproof Boxes & Covers | ■ Flexcor® Wire Mesh Grips |
| ■ TVSS & Isolated Ground Devices     | ■ Turnlok® Locking Devices          | ■ IEC 309 Industrial Products | ■ Bulk Solutions           |
| ■ Ground Continuity Monitoring (GCM) |                                     |                               |                            |

  
Pass & Seymour

P.O. Box 4822  
Syracuse, NY 13221-4822  
Phone: 1.800.776.4035  
[www.legrand.us/passandseymour](http://www.legrand.us/passandseymour)

570 Applewood Crescent  
Vaughan, Ontario L4K 4B4  
Phone: 905.738.9195

